

Manta G-040 is a 0.40 megapixel machine vision camera with a GigE compliant Gigabit Ethernet interface and Hirose port. Manta G-040 incorporates the high quality Type 1/2.9 (6.3 mm diagonal) Sony IMX287 CMOS sensor with Pregius global shutter technology.

### General

Model:	Manta G-040
Product series:	Manta
Status:	Available

### Sensor

Sensor type:	Area scan
Chroma:	Mono or Color
Spectrum:	Visible
Resolution:	728 × 544 (0.40 MP)
Sensor model:	Sony IMX287
Sensor architecture (material):	CMOS
Shutter type(s):	Global Shutter
Sensor size:	6.3 mm ø (Type 1/2.9)
Pixel size:	6.90 µm × 6.90 µm

### Pixel formats

Sensor bit depth:	8-bit or 12-bit
Monochrome pixel formats:	Mono8, Mono12Packed, Mono12
YUV pixel formats:	YUV411Packed, YUV422Packed, YUV444Packed
RGB pixel formats:	RGB8Packed, BGR8Packed
Bayer pixel formats:	BayerRG8, BayerRG12, BayerRG12Packed

### Imaging performance

Quantum efficiency @ 529 nm:	64 %
------------------------------	------

### Timing and gain

Max. frame rate:	286
------------------	-----

## I/Os and power

Specific non-isolated lines:	1
Opto-isolated lines:	2 inputs, 2 outputs
Power supply:	8 to 30 VDC AUX or IEEE 802.3af PoE
Power consumption:	External power: 2.77 W at 12 VDC   Power over Ethernet: 3.23 W

## Operating conditions

Operating temperature (housing):	5 °C to 45 °C ambient (without condensation)
----------------------------------	--

## Mechanical properties

Body dimensions (L x W x H in mm):	86 × 44 × 29
Weight:	190 g

## On-board memory and FPGA

Image buffer (RAM):	128 MByte
Non-volatile memory (Flash):	1024 KByte

## Interfaces

Digital interface:	IEEE 802.3 1000BASE-T, IEEE 802.3af (PoE) optional
--------------------	--

# Quantum Efficiency



