



# Prosilica GT

## Prosilica GT 2000NIR

Prosilica GT2000NIR is a 2.2 megapixel camera with a GigE Vision compliant Gigabit Ethernet port and Hirose I/O port. This camera incorporates a NIR-optimized variant of the high-quality CMOSIS/ams CMV2000 CMOS sensor. At 900 nm this sensor offers double the quantum efficiency, an increase from 8% to 16% absolute.

### General

Model:	Prosilica GT 2000NIR
Product series:	Prosilica GT
Status:	Available

### Sensor

Sensor type:	Area scan
Chroma:	Mono
Spectrum:	Visible-NIR
Resolution:	2,048 × 1,088 (2.20 MP)
Sensor model:	CMOSIS/ams CMV2000 NIR
Sensor architecture (material):	CMOS
Shutter type(s):	Global Shutter
Sensor size:	12.75 mm ø (Type 2/3)
Pixel size:	5.50 µm × 5.50 µm

### Pixel formats

Sensor bit depth:	8-bit or 12-bit
Monochrome pixel formats:	Mono8, Mono12, Mono12Packed

### Imaging performance

Quantum efficiency @ 529 nm:	80 %
Quantum efficiency @ 850 nm:	44 %

### Timing and gain

Max. frame rate:	53 fps
------------------	--------

## I/Os and power

Non-isolated lines:	1 input, 2 outputs
Specific non-isolated lines:	1
Opto-isolated lines:	1 input, 2 outputs
Power supply:	7 to 25 VDC AUX or 802.3at Type 1 PoE
Power consumption:	3.4 W at 12 VDC; 4.2 W PoE

## Operating conditions

Operating temperature (housing):	-20 °C to 65 °C ambient (without condensation)
----------------------------------	--

## Mechanical properties

Body dimensions (L x W x H in mm):	86 × 53 × 33
Weight:	210 g

## On-board memory and FPGA

Image buffer (RAM):	128 MByte
Non-volatile memory (Flash):	1024 KByte

## Interfaces

Digital interface:	IEEE 802.3 1000BASE-T, IEEE 802.3af (PoE)
--------------------	---

# Quantum Efficiency



