



Prosilica GT

Prosilica GT 1930L

Prosilica GT1930L is a 2.35 megapixel camera with a GigE Vision compliant Gigabit Ethernet port and Hirose I/O port. This camera incorporates the high quality Sony IMX174 Exmor CMOS sensor with Pregius global shutter technology providing excellent monochrome and color image quality.

General

Model	Prosilica GT 1930L
Product series	Prosilica GT
Status	Available

Sensor

Sensor type	Area scan
Chroma	Mono or Color
Spectrum	Visible
Resolution	1,936 × 1,216 (2.40 MP)
Sensor model	Sony IMX174
Sensor architecture (material)	CMOS
Shutter type(s)	Global Shutter
Sensor size	13.4 mm ø (Type 1/1.2)
Pixel size	5.86 µm × 5.86 µm

Pixel formats

Sensor bit depth	12-bit
Monochrome pixel formats	Mono8, Mono12Packed, Mono12
YUV pixel formats	YUV411Packed, YUV422Packed, YUV444Packed
RGB pixel formats	RGB8Packed, BGR8Packed
Bayer pixel formats	BayerRG8, BayerRG12, BayerRG12Packed

Imaging performance

Quantum efficiency @ 529 nm	69 %
-----------------------------	------

Timing and gain

Max. frame rate	50 fps
-----------------	--------

I/Os and power

Non-isolated lines	1 input, 2 outputs
Specific non-isolated lines	1
Opto-isolated lines	1 input, 2 outputs
Power supply	7 to 25 VDC AUX or 802.3at Type 1 PoE
Power consumption	3.24 W at 12 VDC; 3.88 W PoE

Operating conditions

Operating temperature (housing)	-30 °C to 70 °C (housing (without condensation))
---------------------------------	--

Mechanical properties

Body dimensions (L x W x H in mm)	96 × 66 × 53
Weight	372 g


On-board memory and FPGA

Image buffer (RAM)	128 MByte
Non-volatile memory (Flash)	1024 KByte

Interfaces

Digital interface	IEEE 802.3 1000BASE-T, IEEE 802.3af (PoE)
-------------------	---

Quantum Efficiency



Technical Drawing

