



Prosilica GT

Prosilica GT 2460

Prosilica GT2460 is a 5.1 megapixel camera with a GigE Vision compliant Gigabit Ethernet port and Hirose I/O port. Prosilica GT2460 is offered as monochrome or color models. This camera incorporates the high quality Sony IMX264 CMOS sensor with Pregius global shutter technology.

General

Model:	Prosilica GT 2460
Product series:	Prosilica GT
Status:	Available

Sensor

Sensor type:	Area scan
Chroma:	Mono or Color
Spectrum:	Visible
Resolution:	2,464 × 2,056 (5.10 MP)
Sensor model:	Sony IMX264
Sensor architecture (material):	CMOS
Shutter type(s):	Global Shutter
Sensor size:	12.75 mm ø (Type 2/3)
Pixel size:	3.45 µm × 3.45 µm

Pixel formats

Sensor bit depth:	12
Monochrome pixel formats:	Mono8, Mono12, Mono12Packed
YUV pixel formats:	YUV411Packed, YUV422Packed, YUV444Packed
RGB pixel formats:	RGB8Packed, BGR8Packed
Bayer pixel formats:	BayerRG8, BayerRG12, BayerRG12Packed

Imaging performance

Quantum efficiency @ 529 nm:	64 %
------------------------------	------

Timing and gain

Max. frame rate: 23 fps

I/Os and power

Non-isolated lines: 1 input, 2 outputs

Specific non-isolated lines: 1

Opto-isolated lines: 1 input, 2 outputs

Power supply: 7 to 25 VDC AUX or 802.3at Type 1 PoE

Power consumption: 3.4 W at 12 VDC; 4.2 W PoE

Operating conditions

Operating temperature (housing): -20 °C to 65 °C ambient (without condensation)

Mechanical properties

Body dimensions (L x W x H in mm): 86 × 53 × 33

Weight: 211 g

On-board memory and FPGA

Image buffer (RAM): 128 MByte

Non-volatile memory (Flash): 1024 KByte

Interfaces

Digital interface: IEEE 802.3 1000BASE-T, IEEE 802.3af (PoE)

Quantum Efficiency



