



allPIXA evo CXP

allPIXA evo 8k CXP Z

General

Model	allPIXA evo 8k CXP Z
Product code	CP000620-S-08K-33-F1-C1-Z
Product series	allPIXA evo CXP
Status	Available

Sensor

Sensor type	Line scan 2D
Chroma	Color+Mono+NIR
Spectrum	Visible-NIR
Spectral range	360 nm to 960 nm
Resolution	8,192 × 4 lines
Sensor architecture (material)	cmos
Pixel size	5.00 μm × 5.00 μm

Pixel formats

Data format	3 × 8/10/12 Bit color or 1 × 8/10/12 Bit mono or 4 × 8/10/12 RGB + NIR
-------------	--

Timing and gain

Max. line rate single-line	100 kHz
Max. line rate tri-linear	100 kHz
Max. line rate quad-linear	100 kHz

I/Os and power

I/O connector	External I/O (15 pin HD D-Sub, fem.)
Power supply	12 V – 24 V DC ± 10 %; 1 A @ 24 V

I/Os and power

Power consumption External: 24 W

Mechanical properties

Body dimensions (L x W x H in mm) 102 × 76 × 82
IP class IP50
Lens mount(s) M72 × 0.75 mm / F-mount
Weight 900 g

On-board memory and FPGA

Non-volatile memory (Flash) 32 KByte


Interfaces

Digital interface 4 × cxp-12 micro-bnc
Interface connector Micro-BNC
Vision standard CoaxPress

FW features - image control

Exposure modes manual
Gain modes auto, manual
White balance modes auto, manual

Quantum Efficiency



Technical Drawing

