



# Prosilica GT

## Prosilica GT 4400

Prosilica GT4400 is a large format camera equipped with a GigE Vision compliant Gigabit Ethernet port and Hirose I/O port. This camera incorporates the second generation Sony IMX367 Exmor CMOS sensor with Pregius global shutter technology.

### General

Model:	Prosilica GT 4400
Product series:	Prosilica GT
Status:	Available

### Sensor

Sensor type:	Area scan
Chroma:	Mono or Color
Spectrum:	Visible
Resolution:	4,432 × 4,436 (19.70 MP)
Sensor model:	Sony IMX367
Sensor architecture (material):	CMOS
Shutter type(s):	Global Shutter
Sensor size:	22.66 mm ø (Type 4/3)
Pixel size:	3.45 µm × 3.45 µm

### Pixel formats

Sensor bit depth:	12-bit
Monochrome pixel formats:	Mono8, Mono12Packed, Mono12
YUV pixel formats:	YUV411Packed, YUV422Packed, YUV444Packed
RGB pixel formats:	RGB8Packed, BGR8Packed
Bayer pixel formats:	BayerRG8, BayerRG12, BayerRG12Packed

### Imaging performance

Quantum efficiency @ 529 nm:	64 %
------------------------------	------

## Timing and gain

Max. frame rate: 6

## I/Os and power

Non-isolated lines: 1 input, 2 outputs

Specific non-isolated lines: 1

Opto-isolated lines: 1 input, 2 outputs

Power supply: 7 to 25 VDC AUX or IEEE 802.3at Type 1 PoE

Power consumption: External power: 5.0 W at 12 VDC | Power over Ethernet: 6.2 W

## Operating conditions

Operating temperature (housing): -20 °C to 50 °C housing (without condensation)

## Mechanical properties

Body dimensions (L x W x H in mm): 96 × 66 × 53

Weight: 372 g

## On-board memory and FPGA

Image buffer (RAM): 128 MByte

Non-volatile memory (Flash): 1024 KByte

## Interfaces

Digital interface: IEEE 802.3 1000BASE-T, IEEE 802.3af (PoE)

# Quantum Efficiency



