



Alecs G1-1242 innovative vision system with Sony IMX545 CMOS global shutter sensor and NVIDIA® Jetson Orin™ NX16 enables developing applications faster.

General

Model	Alecs G1-1242 NX16
Product series	Alecs
Status	Available

Sensor

Sensor type	Area scan
Chroma	Mono or Color
Spectral range	300 nm to 1100 nm
Resolution	4,128 × 3,008 (12.40 MP)
Sensor model	Sony IMX545
Shutter type(s)	Global shutter (GS)
Sensor size	14 mm ø (Type 1/1.1)
Pixel size	2.74 µm × 2.74 µm

Pixel formats

Monochrome pixel formats	GREY, RAW10, RAW12, RAW8, Y10, Y12
YUV pixel formats	UYVY, YCbCr411_8_CbYYCrYY, YCbCr422_8_CbYCrY, YCbCr8_CbYCr, YUV422 8-bit
RGB pixel formats	BGR8, RGB3, RGB8 (default), RGB888 (default)
Bayer pixel formats	BayerRG12

Imaging performance

Quantum efficiency @ 529 nm	68 %
-----------------------------	------

Timing and gain

Max. frame rate	40 fps
-----------------	--------

I/Os and power

Non-isolated lines	2 inputs, 2 outputs, 1 trigger input, 1 strobe output
--------------------	---

Power supply	24 VDC
--------------	--------

Power consumption	SoM: Max. 10 W to 25 W Carrier board: Max. 2.0 W Camera: Max. 3.2 W Idle state: 8.5 W
-------------------	--

Operating conditions

Operating temperature (housing)	-20 °C to 65 °C ((housing))
---------------------------------	-----------------------------

Mechanical properties

Body dimensions (L x W x H in mm)	102 × 72 × 112
-----------------------------------	----------------

Lens mount(s)	C-Mount
---------------	---------

Weight	810 g
--------	-------

On-board memory and FPGA


Image buffer (RAM)	256 KByte
--------------------	-----------

Non-volatile memory (Flash)	1024 KByte
-----------------------------	------------

Interfaces

Digital interface	IEEE 802.3 1000BASE-T
-------------------	-----------------------

Quantum Efficiency



Technical Drawing

 Technical Drawing