





- IEEE 1394a camera
- Modular design
- Robust housing
- Machine vision camera



### Robust housing, modular design

Compact, flexible, modular IEEE 1394a XGA C-Mount camera

Marlin F-033 with Sony ICX414 runs 73.0 frames per second at 0.3 MP resolution.

Acclaimed bestseller digital IEEE 1394 machine vision camera

The Marlin is Allied Vision's classical most-sold IEEE 1394 machine vision camera. Since 2004, many thousand Marlins are part of various different image processing applications. Due to its modular design (angled head, side-entry connectors, Modular Concept), it fits with almost every application.

- IEEE 1394a (400 Mb/s)
- Sony CCD sensors (1/3, 1/2, 1/1.8), 2/3 CMOS sensor
- 7 models (VGA to 2 Megapixel)
- Options
  - Various IR cut/pass filters
  - CS-Mount
  - Angled head
  - Lateral cable exit
  - White medical housing



				٠ ر						
S	n	$\boldsymbol{\triangle}$	$\cap$	$_{1}$ T $_{1}$	$\cap$	Э	ΤI	$\cap$	n	C
$\cup$	U	U.	$\cup$		u	а	UΠ	$\cup$		$\supset$

Interface IEEE 1394a - 400 Mb/s, 1 port

Resolution  $656 (H) \times 494 (V)$ 

Sensor Sony ICX414

Sensor type CCD Progressive

Sensor size Type 1/2

Pixel size  $9.9 \,\mu\text{m} \times 9.9 \,\mu\text{m}$ 

Lens mount (default) C-Mount

Max. frame rate at full resolution 73 fps

ADC 12 Bit

Image buffer (RAM) 8 MByte

### Output

Bit depth 8-bit to 10-bit

Monochrome pixel formats Mono8, Mono16

RGB color pixel formats RGB8

Raw pixel formats Raw8

#### General purpose inputs/outputs (GPIOs)

Opto-isolated I/Os 2 inputs, 2 outputs

RS232 1

#### **Operating conditions/dimensions**

Operating temperature +5 °C to +45 °C

Power requirements (DC) 8 V to 36 V


Power consumption <3 W (@ 12 VDC)

Mass <120 g

Body dimensions (L × W × H in mm) 72 × 44x 29 (including connectors)



## Quantum efficiency






### Features

Marlin cameras are equipped with many useful real-time image pre-processing functions. They are performed by the FPGA inside the camera – with no additional CPU load on the host, so that an inexpensive system is sufficient.

- Programmable look-up table (LUT), white balance, hue, saturation
- Debayering
- Gain
  - Auto/manual
  - Manual gain control: 0 to 24 dB
- Exposure
  - Auto/manual
  - Exposure time: 32 μs to 67 s
- Color correction
- Shading correction
- Sub-sampling, 2x binning (b/w)
- Area of interest (AOI) with speed increase
- Sequence mode changes the image settings on the fly
- Image mirror
- Deferred image transport
- SIS (secure image signature, time stamp for trigger, frame count)
- Storable user settings



# Technical drawing



### Applications

With its modular and flexible design and the real-time pre-processing functions, this Marlin camera fits for many applications:

- Machine vision
- Quality control
- Semiconductor inspection
- Industrial inspection