





- IEEE 1394a camera
- Modular design
- Robust housing
- Machine vision camera



Robust housing, modular design

Compact, flexible, modular IEEE 1394a XGA C-Mount camera

Marlin F-145 with Sony ICX205 runs 10.0 frames per second at 1.4 MP resolution.

Acclaimed bestseller digital IEEE 1394 machine vision camera

The Marlin is Allied Vision's classical most-sold IEEE 1394 machine vision camera. Since 2004, many thousand Marlins are part of various different image processing applications. Due to its modular design (angled head, side-entry connectors, Modular Concept), it fits with almost every application.

- IEEE 1394a (400 Mb/s)
- Sony CCD sensors (1/3, 1/2, 1/1.8), 2/3 CMOS sensor
- 7 models (VGA to 2 Megapixel)
- Options
 - Various IR cut/pass filters
 - CS-Mount
 - Angled head
 - Lateral cable exit
 - White medical housing



		' (
\sim r	$\gamma \triangle C$	ıtıca	$TI\cap$	nc
\sim 1	ノしし	$\Pi \Pi \cup \mathcal{O}$	ししし	

Interface IEEE 1394a - 400 Mb/s, 1 port

Resolution 1392 (H) \times 1040 (V)

Sensor Sony ICX205

Sensor type CCD Progressive

Sensor size Type 1/2

Pixel size $4.65 \,\mu\text{m} \times 4.65 \,\mu\text{m}$

Lens mount (default) C-Mount

Max. frame rate at full resolution 10 fps

ADC 12 Bit

Image buffer (RAM) 8 MByte

Output

Bit depth 8-bit to 10-bit

Monochrome pixel formats Mono8, Mono16

RGB color pixel formats RGB8

Raw pixel formats Raw8

General purpose inputs/outputs (GPIOs)

Opto-isolated I/Os 2 inputs, 2 outputs

RS232 1

Operating conditions/dimensions

Operating temperature +5 °C to +45 °C

Power requirements (DC) 8 V to 36 V


Power consumption <3 W (@ 12 VDC)

Mass <120 g

Body dimensions (L × W × H in mm) 72 × 44x 29 (including connectors)



Quantum efficiency






Features

Marlin cameras are equipped with many useful real-time image pre-processing functions. They are performed by the FPGA inside the camera – with no additional CPU load on the host, so that an inexpensive system is sufficient.

- Programmable look-up table (LUT), white balance, hue, saturation
- Debayering
- Gain
 - Auto/manual
 - Manual gain control: 0 to 24 dB
- Exposure
 - Auto/manual
 - Exposure time: 38 μs to 67 s
- Color correction
- Shading correction
- Sub-sampling, 2x binning (b/w)
- Area of interest (AOI) with speed increase
- Sequence mode changes the image settings on the fly
- Image mirror
- Deferred image transport
- SIS (secure image signature, time stamp for trigger, frame count)
- Storable user settings



Technical drawing



Applications

With its modular and flexible design and the real-time pre-processing functions, this Marlin camera fits for many applications:

- Machine vision
- Quality control
- Industrial inspection