







- Advanced feature set
- · Many variants
- High frame rates



High-end FireWire

Fast 1394b cameras with high frame rates and powerful features

Pike F-505 搭载 Sony ICX625 传感器,在 5.0 MP 分辨率下速度可达 14.0 帧/秒。

The Pike is a fast IEEE 1394b camera for demanding applications (e.g. industrial and medical imaging). Numerous pre-processing functions produce an outstanding image quality. Pike cameras operate with very high frame rates.

Pike cameras include extraordinary image pre-processing functions like the High SNR mode (up to 24 dB better signal-to-noise ratio).

Pike cameras are available both with two copper ports (for daisy-chaining) and with copper/GOF (glass optical fiber) ports.

- Sony and OnSemi CCD sensors (1/3, 1/2, 2/3, 1, 1.2, 35 mm)
- 8 models (VGA to 16 Megapixel)
- Options
 - 1394b connectors: daisy chain copper or copper and GOF
 - Various IR cut/pass filters
 - F/M39-Mount (F-032 only: CS/M12-Mount)
 - Pike F-1100/F-1600: M42/M58-Mount
 - Hirose power: out
 - Angled head
 - White medical housing
 - Sensor variants: Taped cover glass w/o microlenses, fixed quartz cover glass w/o microlenses available for some models



Lal	. AL	4	NL
11.4	巨口	灰	套U

接口 IEEE 1394b - 800 Mb/s, 2 ports, daisy chain, fiber optic

(GOF) optional

分辨率 2452 (H) × 2054 (V)

传感器 Sony ICX625

传感器类型 CCD Progressive

传感器尺寸 Type 2/3

像元尺寸 3.45 μm × 3.45 μm

标准镜头接口 C-Mount

最大满帧帧率 14 fps

ADC 14 Bit

缓存 (RAM) 64 MByte

输出

Bit 位数 8-bit to 14-bit

黑白像素格式 Mono8, Mono12, Mono16

RGB 彩色像素格式 RGB8

原始像素格式 Raw8, Raw12, Raw16

通用输入输出口(GPIOs)

光耦 I/Os 2 inputs, 4 outputs

RS232 1

工作条件/尺寸

工作温度 +5 °C to +50 °C

电源要求 (DC) 8 V to 36 V


功耗 4 W (@ 12 VDC)

重量 250 g

尺寸 (L×W×H in mm) 96.8×44×44 (including connectors)



量子转换效率







特性


- High SNR mode (up to 24 dB better signal-to-noise ratio)
- Low-noise binning mode
- Smear reduction
- Shading correction
- Area of interest (AOI), separate AOI for auto features
- Binning
- Decimation
- Auto gain (manual gain control: 0 to 24 dB)
- Auto exposure (27 μs to 67 s)
- Auto white balance
- Look-up table (LUT)
- Hue, saturation, color correction
- Reverse X
- Deferred image transport
- Trigger programmable, level, single, bulk, programmable delay
- Sequence mode (changes the camera settings on the fly)
- SIS (secure image signature, time stamp for trigger, frame count)
- Storable user sets




外形尺寸









应用场景

The Pike F-505B/F-505C is perfectly suited for very demanding applications. The brillant image quality can be enhanced by its image pre-processing functions. Due to the modular design, customization is easy and cost-effective. This camera fits especially for:

- Science and research
- Microscopy
- Healthcare and medical applications (white housing available)
- Multimedia, entertainment and sports
- Very demanding OEM camera applications



- ITS (Intelligent traffic solutions)
 Long cables 400 meters and more without additional repeaters (fiber version)