

Prosilica GC

650



- Sony ICX424 sensor
- 90 fps @ full resolution
- Rugged housing
- Video-type auto iris

Description

Very small VGA CCD camera with GigE Vision, 90 frames per second

Prosilica GC650 is a fast, VGA-resolution, high-performance machine vision camera with a GigE Vision compliant Gigabit Ethernet interface. The Sony ICX424 CCD sensor with HAD technology has excellent image quality and sensitivity. This camera is suitable for applications where speed and excellent image quality are key requirements. At full resolution, this camera has a frame rate of 90 frames per second. With a smaller region of interest higher frame rates are possible. By default monochrome models ship with no optical filter and color models ship with an IRC30 IR cut filter.

Options:


- CS-Mount
- Optical filters (IR cut filter/Protection glass)

See the [Modular Concept](#) for lens mount and optical filter options.

Specifications

Prosilica GC	650
Interface	IEEE 802.3 1000baseT
Resolution	659 (H) × 493 (V)
Sensor	Sony ICX424
Sensor type	CCD Progressive
Sensor size	Type 1/3
Pixel size	7.4 μm × 7.4 μm

Prosilica GC		650	
Lens mount (default)		C-Mount	
Max. frame rate at full resolution		90 fps	
ADC		12 bit	
Image buffer (RAM)		16 MByte	
Output			
Bit depth		8/12 bit	
Monochrome pixel formats		Mono8, Mono12, Mono12Packed	
RGB color pixel formats		RGB8Packed, BGR8Packed	
Raw pixel formats		BayerRG8, BayerRG12, BayerGR12Packed	
General purpose inputs/outputs (GPIOs)			
TTL I/Os		1 input, 1 output	
Opto-isolated I/Os		1 input, 1 output	
RS232		1	
Operating conditions/dimensions			
Operating temperature		0 °C to +50 °C ambient (without condensation)	
Power requirements (DC)		5 to 25 VDC	
Power consumption		3 W at 12 VDC	
Mass		99 g	
Body dimensions (L × W × H in mm)		59 × 46 × 33 (including connectors)	
Regulations		CE: 2014/30/EU (EMC), 2011/65/EU, including amendment 2015/863/EU (RoHS); FCC Class A; CAN ICES-003	





Features


Image optimization features:

- Auto gain (manual gain control: 0 to 19 dB)
- Auto exposure (manual exposure control: 8 μ s to 116.8 s @ 1 μ s increments)
- Auto white balance
- Binning (horizontal and vertical) (sum)
- Region of interest (ROI), DSP subregion (selectable ROI for auto features)

Camera control features:

- Auto-iris (video type)
- Event channel
- Global shutter (digital shutter)
- IEEE 1588 Precision Time Protocol
- Image chunk data
- Recorder and Multiframe acquisition modes
- RS232
- Five storable user sets
- StreamBytesPerSecond (bandwidth control)
- Stream hold
- Sync out modes: Trigger ready, input, exposing, readout, imaging, strobe, GPO

Technical drawing





Applications

Prosilica GC650 is ideal for a wide range of applications including:

- Machine vision
- Industrial inspection
- Public security
- Traffic monitoring
- Robotics