

## Mako U U-029



- Latest CMOS sensor
- High frame rates
- Ultra-compact
- Extensively tested accessories

### Description

#### Mako U-029B with CMOS ON Semi PYTHON 300 sensor

Mako U-029B is a monochrome USB3 Vision camera with the ON Semiconductor PYTHON 300 CMOS sensor. All Mako USB cameras have the same compact housing with a form factor of 49.5 x 29 x 29 mm. Screw locks ensure a safe electrical connection even in harsh industrial environments.

Every model is powered over the USB interface and has opto-isolated I/Os. The GPIOs give Mako U maximum flexibility to adapt to specific needs. The two non-isolated GPIO lines are TTL-based and programmable as input or output.


Options:

- Various IR cut/pass filters, protection glass, various lens mounts
- White medical housing

### Specifications

Mako U	U-029
インターフェイス	USB3 Vision
解像度	640 (H) × 480 (V)
センサー	ON Semi PYTHON 300
Sensor type	CMOS
センサーサイズ	Type 1/4
ピクセルサイズ	4.8 μm × 4.8 μm
レンズマウント (標準搭載)	C-Mount, CS-Mount
フレームレート (フル解像度)	550 fps
ADC	10 bit
Image buffer (RAM)	128 MByte

Mako U	U-029
	Output
Bit depth	8/10 bit
ビデオフォーマット(Mono)	Mono8, Mono10p
	General purpose inputs/outputs (GPIOs)
TTL I/Os	2 programmable GPIOs
Opto-isolated I/Os	1 input, 1 output
	Operating conditions/dimensions
Operating temperature	+5 °C to +45 °C (housing temperature)
Power requirements (DC)	Power over USB 3.0
消費電力	2.7 W @ 5 VDC
Mass	60 g
Body dimensions (L × W × H in mm)	49.5 × 29 × 29 (including connectors)
Regulations	CE: 2014/30/EU (EMC), 2011/65/EU, incl. amendment 2015/863/EU (RoHS); FCC Class B




## Features

- Defect pixel correction (on/off)
- Fixed pattern noise correction (on/off)
- Region of interest (ROI)
- Gain (manual control, 0 to 20 dB)
- Exposure (manual control, 44.2 μs to 1.4 s)
- Gamma correction

- Reverse X
- DeviceLinkThroughputLimit (easy bandwidth control)
- Sync out modes: Waiting for a trigger, exposing, readout, imaging
- Storable user sets

## Technical drawing





## Applications

The Mako U is an inexpensive USB 3.0 camera with a compact housing. USB 3.0 technology has lower latency and jitter times with less CPU load than other camera interfaces.

Typical applications for Mako U cameras:

- Machine vision
- Quality control
- Inspection, surveillance
- Industrial imaging