

Prosilica GS

660



- Right-angle CCD camera with low height profile
- High frame rate
- Video-type auto iris
- Sony ICX618 sensor

Description


Right-angle GigE Vision camera, Sony ICX618 EXview sensor, 119 fps

Prosilica GS660 is a fast, VGA resolution, high-performance machine vision camera with Gigabit Ethernet interface. This camera incorporates a Sony ICX618 EXview HAD CCD sensor that has particularly high quantum efficiency and excellent NIR response for excellent image quality and sensitivity. At full resolution, this camera has a frame rate of 119 frames per second. With a smaller region of interest higher frame rates are possible. By default monochrome models ship with no optical filter and color models ship with an IRC30 IR cut filter.

Specifications

| Prosilica GS | 660 |
|------------------------------------|-----------------------------|
| Interface | IEEE 802.3 1000baseT |
| Resolution | 659 (H) × 493 (V) |
| Sensor | Sony ICX618 |
| Sensor type | CCD Progressive |
| Sensor size | Type 1/4 |
| Pixel size | 5.6 μm × 5.6 μm |
| Lens mount (default) | C-Mount |
| Max. frame rate at full resolution | 119 fps |
| ADC | 14 bit |
| Image buffer (RAM) | 16 MByte |
| | Output |
| Bit depth | 8/12 bit |
| Monochrome pixel formats | Mono8, Mono12, Mono12Packed |

| | |
|---|---|
| Prosilica GS | 660 |
| YUV color pixel formats | YUV411Packed, YUV422Packed, YUV444Packed |
| RGB color pixel formats | RGB8Packed, BGR8Packed |
| Raw pixel formats | BayerRG8, BayerRG12, BayerGR12Packed |
| General purpose inputs/outputs (GPIOs) | |
| TTL I/Os | 1 input, 1 output |
| Opto-isolated I/Os | 1 input, 1 output |
| RS232 | 1 |
| Operating conditions/dimensions | |
| Operating temperature | 0 °C to +70 °C ambient (without condensation) |
| Power requirements (DC) | 5 to 25 VDC |
| Power consumption | 3 W at 12 VDC |
| Mass | 184 g |
| Body dimensions (L × W × H in mm) | 96 × 56 × 26 (including connectors) |
| Regulations | CE: 2014/30/EU (EMC), 2011/65/EU, including amendment 2015/863/EU (RoHS); FCC Class A |



Features


Prosilica GS660 features include:

- Auto-iris (video type)
- Region of interest (ROI), DSP subregion (selectable ROI for auto features)
- Binning (Sum)



- Auto gain (manual gain control: 0 to 30 dB)
- Auto exposure (manual exposure controls: 10 μ s to 78.5 s)
- Auto white balance
- StreamBytesPerSecond (bandwidth control)
- Stream hold
- Sync out modes: Trigger ready, input, exposing, readout, imaging, strobe, GPO
- Global shutter (digital shutter)
- Recorder and Multiframe acquisition modes
- Event channel
- Image chunk data
- Storable user sets

Technical drawing





Applications

Prosilica GS660 is ideal for a wide range of applications including:

- Machine vision
- Industrial inspection
- Public security
- Traffic monitoring
- Microscopy