

allPIXA evo CXP

allPIXA evo 32K CXP Mono Y



General

Model:	allPIXA evo 32K CXP Mono Y
Product code:	CP000620-S-32K-33-L1-M-Y
Product series:	allPIXA evo CXP
Status:	Available

Sensor

Sensor type:	Line scan 2D
Chroma:	Mono
Spectrum:	Visible-NIR
Spectral range:	400 nm to 1000 nm
Resolution:	32,768 × 1 lines
Sensor architecture (material):	cmos
Pixel size:	5.00 µm × 5.00 µm

Pixel formats

Data format:	1 × 8/10/12 Bit mono
--------------	----------------------

Timing and gain

Max. line rate single-line:	73 kHz
-----------------------------	--------

I/Os and power

I/O connector:	External I/O (15 pin HD D-Sub, fem.)
----------------	--------------------------------------

I/Os and power

Power supply:	12 to 24 VDC, PoCXP
Power consumption:	External: 24 W

Mechanical properties

Body dimensions (L x W x H in mm):	102 × 102 × 113
IP class:	IP50
Lens mount(s):	M95 × 1 mm
Weight:	1100 g

On-board memory and FPGA

Non-volatile memory (Flash):	32 KByte
------------------------------	----------

Interfaces

Digital interface:	cxp-12 with 4 connections
Interface connector:	Micro-BNC
Vision standard:	CoaxPress

FW features - image control

Exposure modes:	manual
Gain modes:	auto, manual
White balance modes:	auto, manual

Quantum Efficiency



