







- IEEE 1394a camera
- Lightweight
- Robust design
- · Machine vision camera

Lightweight and robust

Guppy - Ultra-compact camera with IEEE 1394a interface

Guppy F-046 with Sony ICX415 runs 49.0 frames per second at 0.5 MP resolution.

Guppy is an ultra-compact, inexpensive IEEE 1394a VGA machine vision camera. This reliable mainstream FireWire camera addresses a wide range of imaging applications. With its ultra-compact, small housing, Guppy is the perfect fit for all applications with space constraints.

Easy software integration with Allied Vision's Vimba Suite and compatibility to the most popular third party image-processing libraries.

See the Customization and OEM Solutions webpage for hardware options.



$\leq r$	$\Delta \cap$	ITIC	rati	ons
-	\mathcal{L}		Jali	OIIO

Interface IEEE 1394a - 400 Mb/s, 1 port

Resolution 780 (H) \times 582 (V)

Sensor Sony ICX415

Sensor type CCD Progressive

Sensor size Type 1/2

Pixel size $8.3 \,\mu\text{m} \times 8.3 \,\mu\text{m}$

Lens mount (default) C-Mount, CS-Mount

Max. frame rate at full resolution 49 fps

ADC 12 Bit

Output

Bit depth 8-bit

Monochrome pixel formats Mono8

RGB color pixel formats n/a

Raw pixel formats Raw8

General purpose inputs/outputs (GPIOs)

TTL I/Os 1 input, 3 outputs

RS232 1

Operating conditions/dimensions

Operating temperature +5 °C to +45 °C

Power requirements (DC) 8 V to 36 V


Power consumption <2 W (@ 12 VDC)

Mass 50 g

Body dimensions (L \times W \times H in mm) 48.2 \times 30 \times 30 (including connectors)



Quantum efficiency






Features

- Look-up table (LUT)
- Area of interest (AOI), separate AOI for auto features
- Auto gain (0 to 24 dB)
- Auto exposure (42 μs to 67 s)
- Auto white balance
- Storable user sets



Technical drawing



Applications

This inexpensive, reliable mainstream 0.5 Megapixel camera addresses a wide range of imaging applications (e.g. robotics). With its ultra-compact housing, the Guppy F-046B/F-046C is the perfect fit for all applications with space constraints.



- Machine vision
- Robotics (robust, lightweight housing)
- Quality control
- Ophthalmology
- Semiconductor inspection
- Industrial inspection
- ITS/Traffic monitoring