


# Prosilica GB

## 1380



- Single board
- 30 fps @ full resolution
- Landscape or portrait sensor orientation
- Auto-iris (video type)

## Description

### 1.4 Megapixel single-board GigE Vision camera - high sensitivity

Prosilica GB1380 is a very sensitive, high-resolution CCD camera with Gigabit Ethernet interface. This camera incorporates the high quality Type 2/3 (11.0 mm diagonal) Sony ICX285 CCD sensor with EXview technology providing high-sensitivity, low noise, excellent anti-blooming, and superb image quality. At full resolution, this camera runs 30 frames per second. With a smaller region of interest, higher frame rates are possible. By default monochrome models ship with no optical filter and color models ship with an IRC30 IR cut filter.


#### Options:

- Portrait or landscape sensor orientation
- Inline or vertical connector orientation

## Specifications

Prosilica GB	1380
インターフェイス	IEEE 802.3 1000baseT
解像度	1360 (H) × 1024 (V)
センサー	Sony ICX285
Sensor type	CCD Progressive
センサーサイズ	Type 2/3
ピクセルサイズ	6.45 μm × 6.45 μm
レンズマウント (標準搭載)	C-Mount
フレームレート (フル解像度)	30 fps
ADC	14 bit

Prosilica GB	1380
Image buffer (RAM)	16 MByte
<b>Output</b>	
Bit depth	8/12 bit
ビデオフォーマット(Mono)	Mono8, Mono12, Mono12Packed
ビデオフォーマット(YUV)	YUV411Packed, YUV422Packed, YUV444Packed
ビデオフォーマット(RGB)	RGB8Packed, BGR8Packed
ビデオフォーマット(Raw)	BayerRG8, BayerRG12, BayerGR12Packed
<b>General purpose inputs/outputs (GPIOs)</b>	
TTL I/Os	1 input, 1 output
Opto-isolated I/Os	1 input, 1 output
RS232	1
<b>Operating conditions/dimensions</b>	
Operating temperature	0 °C to +70 °C
Power requirements (DC)	5 to 25 VDC
消費電力	3.5 W at 12 VDC
Mass	59 g
Body dimensions (L × W × H in mm)	51 × 89 (board size - W × L)
Regulations	2011/65/EU, including amendment 2015/863/EU (RoHS)





## Features

### Image optimization features:

- Auto gain (manual gain control: 0 to 30 dB; 1 dB increments)
- Auto exposure (manual exposure control: 10  $\mu$ s to 78.5 s; 1  $\mu$ s increments)
- Auto white balance (GB1380C only)
- Binning (horizontal and vertical) (sum)
- Region of interest (ROI), DSP subregion (selectable ROI for auto features)

### Camera control features:

- Auto-iris (video type)
- Event channel
- Global shutter (digital shutter)
- Image chunk data
- Recorder and Multiframe acquisition modes
- RS232
- Storable user sets
- StreamBytesPerSecond (bandwidth control)
- Stream hold
- Sync out modes: Trigger ready, input, exposing, readout, imaging, strobe, GPO



## Applications

Prosilica GB1380 is ideal for a wide range of applications including:

- Industrial inspection
- Machine vision
- Microscopy
- Ophthalmology
- Fluorescence
- Aeronautical and aerospace
- Public security
- Surveillance
- Traffic imaging