



## Alvium C

### Alvium 1800 C-203

Alvium 1800 C-203 innovative MIPI CSI-2 camera with Sony IMX422 CMOS global shutter sensor provides industrial performance for cost effective embedded and machine vision applications.

#### General

|                |                   |
|----------------|-------------------|
| Model          | Alvium 1800 C-203 |
| Product series | Alvium C          |
| Status         | Available         |

#### Sensor

|                                |                                   |
|--------------------------------|-----------------------------------|
| Sensor type                    | Area scan                         |
| Chroma                         | Color, Mono                       |
| Spectrum                       | Visible                           |
| Spectral range                 | 300 nm to 1100 nm                 |
| Resolution                     | 1,632 × 1,248 (2.00 MP)           |
| Sensor model                   | Sony IMX422                       |
| Sensor architecture (material) | cmos                              |
| Shutter type(s)                | Global shutter (GS)               |
| Sensor size                    | 7.3 × 5.6 mm (9.2 mm, Type 1/1.7) |
| Pixel size                     | 4.50 µm × 4.50 µm                 |

#### Pixel formats

|                          |                                                                          |
|--------------------------|--------------------------------------------------------------------------|
| Sensor bit depth         | 10-bit, 12-bit, 8-bit                                                    |
| Monochrome pixel formats | GREY, RAW10, RAW12, RAW8, Y10, Y12                                       |
| YUV pixel formats        | UYVY, YCbCr411_8_CbYYCrYY, YCbCr422_8_CbYCrY, YCbCr8_CbYCr, YUV422 8-bit |
| RGB pixel formats        | BGR8, RGB3, RGB8 (default), RGB888 (default)                             |
| Bayer pixel formats      | BayerGR10, BayerGR10p, BayerGR12, BayerGR12p, BayerGR8                   |

## Timing and gain

|                 |                    |
|-----------------|--------------------|
| Max. frame rate | 225 fps            |
| Exposure time   | 18 $\mu$ s to 10 s |
| Gain            | 0.0 dB to 48.0 dB  |

## I/Os and power

|                    |                       |
|--------------------|-----------------------|
| Non-isolated lines | 2 programmable GPIOs  |
| Power supply       | 5 VDC over MIPI CSI-2 |
| Power consumption  | Typical: 3.1 W        |

## Operating conditions

|                                 |                             |
|---------------------------------|-----------------------------|
| Operating temperature (housing) | -20 °C to 65 °C ((housing)) |
|---------------------------------|-----------------------------|

## Mechanical properties

|                                   |                   |
|-----------------------------------|-------------------|
| Body dimensions (L x W x H in mm) | 26 × 29 × 29      |
| Lens mount(s)                     | C-Mount, CS-Mount |
| Weight                            | 40 g              |


## On-board memory and FPGA

|                             |            |
|-----------------------------|------------|
| Image buffer (RAM)          | 256 KByte  |
| Non-volatile memory (Flash) | 1024 KByte |

## Interfaces

|                   |                           |
|-------------------|---------------------------|
| Digital interface | MIPI CSI-2, up to 4 lanes |
|-------------------|---------------------------|

## Quantum Efficiency



## Technical Drawing

