

Prosilica GC 2450



- Sony ICX625 CCD sensor
- 15 fps @ full resolution
- Rugged housing
- Video-type auto iris

Description

GigE Vision, Sony ICX625 CCD sensor, auto-iris, 15 fps

Prosilica GC2450 is a 5.0 Megapixel camera with a GigE Vision compliant Gigabit Ethernet port and Hirose I/O port. Prosilica GC2450 is offered in both monochrome and color models. This camera incorporates the high quality Type 2/3 (11.016 mm diagonal) Sony ICX625 CCD sensor with Super HAD CCD technology that provides superior image quality, excellent sensitivity, and low noise. At full resolution, this camera has a frame rate of 15 frames per second. With a smaller region of interest higher frame rates are possible. By default monochrome models ship with no optical filter and color models ship with an IRC30 IR cut filter.

Benefits and features:

- Monochrome (GC2450) and color (GC2450C) models
- Screw mount RJ45 Ethernet connector for industrial environments
- Supports cable lengths up to 100 meters (CAT-5e or CAT-6)
- Popular C-Mount lens mount
- Standard M3 mounting holes and optional tripod adapter
- Support for popular third party image-processing libraries including Cognex VisionPro, MathWorks MATLAB, and National Instruments LabVIEW


Options:

- CS-Mount
- Optical filters (IR cut filter/Protection glass)

See the [Modular Concept](#) for lens mount and optical filter options.

Specifications

| | |
|--|---|
| Prosilica GC | 2450 |
| インターフェイス | IEEE 802.3 1000baseT |
| 解像度 | 2448 (H) × 2050 (V) |
| センサー | Sony ICX625 |
| Sensor type | CCD Progressive |
| センサーサイズ | Type 2/3 |
| ピクセルサイズ | 3.45 μm × 3.45 μm |
| レンズマウント (標準搭載) | C-Mount |
| フレームレート (フル解像度) | 15 fps |
| ADC | 12 bit |
| Image buffer (RAM) | 64 MByte |
| Output | |
| Bit depth | 8/12 bit |
| ビデオフォーマット(Mono) | Mono8, Mono12, Mono12Packed |
| ビデオフォーマット(RGB) | RGB8Packed, BGR8Packed |
| ビデオフォーマット(Raw) | BayerRG8, BayerRG12, BayerGR12Packed |
| General purpose inputs/outputs (GPIOs) | |
| TTL I/Os | 1 input, 1 output |
| Opto-isolated I/Os | 1 input, 1 output |
| RS232 | 1 |
| Operating conditions/dimensions | |
| Operating temperature | 0 °C to +40 °C ambient (without condensation) |
| Power requirements (DC) | 5 to 25 VDC |
| 消費電力 | 3.8 W at 12 VDC |
| Mass | 106 g |
| Body dimensions (L × W × H in mm) | 59 × 46 × 33 (including connectors) |
| Regulations | CE: 2014/30/EU (EMC), 2011/65/EU, including amendment 2015/863/EU (RoHS); FCC Class A; CAN ICES-003 |



Features

Image optimization features:


- Auto gain (manual gain control: 0 to 24 dB, 1 dB increments)
- Auto exposure (manual exposure control: 10 μ s to 48.0 s; 1 μ s increments)
- Auto white balance (GC2450C only)
- Binning (horizontal and vertical) (sum)
- Black level (Offset)
- Gamma correction
- Hue, saturation, color transformation (GC2450C only)
- Three look-up tables (LUTs)
- Region of interest (ROI), DSP subregion (selectable ROI for auto features)

Camera control features:

- Auto-iris (video type)
- Event channel
- Global shutter (digital shutter)
- IEEE 1588 Precision Time Protocol
- Image chunk data
- Recorder and Multiframe acquisition modes
- RS232
- Three storable user sets
- StreamBytesPerSecond (bandwidth control)

- StreamHoldCapacity (Up to 12 frames at full resolution)
- Sync out modes: Trigger ready, input, exposing, readout, imaging, strobe, GPO
- Temperature monitoring (mainboard only)

Technical drawing





Applications

Prosilica GC2450 is ideal for a wide range of applications including:

- High-resolution industrial inspection
- LCD panel inspection
- Machine vision
- 3D metrology
- Public security
- Surveillance
- Traffic imaging/Intelligent Traffic Systems (ITS)
- Embedded systems
- OEM applications