

Goldeye CL

Goldeye CL-034 SWIR TEC1

The Goldeye CL-034 TEC1 high-speed camera is one of the fastest VGA resolution short wave infrared (SWIR) cameras with Camera Link interface. Frame rates up to 303 fps at full resolution enable you to access versatile application fields and to speed up your processes.

General

Model	Goldeye CL-034 SWIR TEC1
Product series	Goldeye CL
Status	Available

Sensor

Sensor type	Area scan
Chroma	Mono
Spectrum	SWIR
Spectral range	900 nm to 1700 nm
Resolution	636 × 508 (0.32 MP)
Sensor model	Progressive scan 0.32 MP
Sensor architecture (material)	cmos-ingaas
Shutter type(s)	Global shutter (GS)
Sensor size	9.54 × 7.62 mm (12.2 mm, Type 1)
Pixel size	15.00 µm × 15.00 µm

Pixel formats

Sensor bit depth	14-bit
Monochrome pixel formats	Tap geometry 1X 1Y: Mono8, Tap geometry 1X2 1Y: Mono8

Timing and gain

Max. frame rate	303 fps
Exposure time	1 µs to 200.00 ms
Gain	0.0 dB to 33.0 dB

I/Os and power

Non-isolated lines	LVTTL I/Os: 1 input, 1 output
Specific non-isolated lines	115 200 Baud, 8N1 (adjustable)
Opto-isolated lines	1 input, 2 outputs
Power supply	10.8 V to 30.0 V
Power consumption	11.8 W at 12 VDC

Operating conditions

Operating temperature (housing)	-20 °C to 55 °C ((housing))
---------------------------------	-----------------------------

Mechanical properties

Body dimensions (L x W x H in mm)	78 × 55 × 55
Weight	350 g


On-board memory and FPGA

Image buffer (RAM)	256 MByte
--------------------	-----------

Interfaces

Digital interface	Camera Link Base
-------------------	------------------

Quantum Efficiency



Technical Drawing

