



HR CoaXPress

hr342MCX

一般

型號	hr342MCX
產品編號	F004072
產品系列	HR CoaXPress
狀態	Available

感測器

感測器類型	Area scan
色度	Mono
光譜	Visible
光譜範圍	400 nm to 1000 nm
解析度	6,464 × 4,852 (31.40 MP)
感測器型號	Sony IMX342
感測器架構 (材料)	cmos
快門類型	Global shutter (GS)
感測器尺寸	22.3 × 16.74 mm (27.88 mm, Type APS-C)
像素大小	3.45 µm × 3.45 µm

像素格式

感測器位深	8-bit, 12-bit
單色像素格式	mono8, mono12

影像性能

動態範圍	70.5 dB
訊噪比	39.9 dB

時序與增益

最大影格率	35.7 fps
曝光時間	19 μ s to 60 s
增益	0.0 dB to 48.0 dB

I/O 與電源

非隔離線	0 x LVDS input, 0 x LVDS output, 0 x TTL input, 0 x TTL output, 2 x 24V input, 4 x Open drain output,
特定非隔離線	1 x RS232 input, 1 x RS232 output, 0 x RS422 input, 0 x RS422 output,
光隔離線	1 x Optical isolated input, 0 x Optical isolated input,
I/O 連接器	12-pin Hirose HR10A-10P-12S
電源供應	10 to 25VDC, Power over CoaXPress
功耗	External: 12 W (typical)

操作條件

操作溫度 (機殼)	-10 °C to 65 °C
-----------	-----------------

機械特性

機殼尺寸 (長 x 寬 x 高 mm)	78 x 70 x 70
濾光片/保護玻璃	N-BK7 - AR coating
防護等級	IP30
鏡頭接口	M58x0.75
重量	400 g

板載記憶體與 FPGA

非揮發性記憶體 (Flash)	160 MByte
-----------------	-----------

介面

數位介面	cxp-6 with 4 connections
介面連接器	(Din1.0/2.3)
視覺標準	CoaXPress 1.0

FW 功能 – 影像控制

曝光模式	manual, auto
------	--------------


FW 功能 – 影像控制

增益模式	auto, manual
影像控制功能	roi, lut, mirror-image, dpc, shading-correction, ffc

FW 功能 – 相機控制

觸發模式/同步	internal, software, external
相機控制功能	PoCxP, User Sets, PWM(4), Sequencer,

量子效率



Front

Top

Technical drawing of the front view of a square plate. The plate has a central circular hole with a diameter of 64 mm. The plate has a square hole in the center with dimensions 62 mm by 62 mm and 70 mm by 70 mm. The outer square plate has a thickness of 6.5 mm. There are four corner holes, each with a diameter of 64 mm, and four M4 screws are shown. The drawing is labeled 'Front' and 'Top'.

section

4 x $\varnothing$ 3,3 ∇ 5
M4 - 6H ∇ 4,3
(on top/left/right/bottom)


SVS-VISTEK
HR

74,1
67,2
62,1
56,8
35,7
23,7
11,48
3,68
0


Sensor distance

Technical drawing of the SVS-VISTEK HR unit, showing a side view and a top view. The side view shows a rectangular unit with a height of 1000 mm and a width of 600 mm. The top view shows a rectangular unit with a width of 600 mm and a depth of 200 mm. The unit is labeled "SVS-VISTEK HR".


top view



bottom view



3D view



I/O 引腳分配



Hirose 12 Pin

1	VIN -	(GND)	7	OUT 1	(open drain)
2	VIN +	(10 V to 25 V DC)	8	OUT 2	(open drain)
3	IN 4	(RXD RS232)	9	IN 3 +	(opto In +)
4	OUT 4	(TXD RS232)	10	IN 3 -	(opto In -)
5	IN 1	(0-24V)	11	OUT 3	(open drain)
6	IN 2	(0-24V)	12	OUT 0	(open drain)