



## FXO 25GigE

fxo536C25GE-RF

Preliminary product information. Features and technical specifications are subject to change without notice.

### General

|                |                              |
|----------------|------------------------------|
| Model          | fxo536C25GE-RF               |
| Product code   | F002484                      |
| Product series | FXO 25GigE                   |
| Status         | Prototype/engineering sample |

### Sensor

|                                |                                   |
|--------------------------------|-----------------------------------|
| Sensor type                    | Area scan                         |
| Chroma                         | Color                             |
| Spectrum                       | Visible                           |
| Spectral range                 | 400 nm to 1000 nm                 |
| Resolution                     | 2,848 × 2,848 (8.10 MP)           |
| Sensor model                   | Sony IMX536                       |
| Sensor architecture (material) | cmos                              |
| Shutter type(s)                | Global shutter (GS)               |
| Sensor size                    | 7.8 × 7.8 mm (11.04 mm, Type 2/3) |
| Pixel size                     | 2.74 μm × 2.74 μm                 |

### Pixel formats

|                   |                 |
|-------------------|-----------------|
| Sensor bit depth  | 8-bit, 12-bit   |
| RGB pixel formats | bayer8, bayer12 |

### Imaging performance

|               |       |
|---------------|-------|
| Dynamic range | 72 dB |
| SNR           | 39 dB |

## Timing and gain

|                 |                   |
|-----------------|-------------------|
| Max. frame rate | 195 fps           |
| Exposure time   | 4 $\mu$ s to 60 s |
| Gain            | 0.0 dB to 48.0 dB |

## I/Os and power

|                             |                                                                                                       |
|-----------------------------|-------------------------------------------------------------------------------------------------------|
| Non-isolated lines          | 0 x LVDS input, 0 x LVDS output, 0 x TTL input, 0 x TTL output, 2 x 24V input, 4 x Open drain output, |
| Specific non-isolated lines | 1 x RS232 input, 1 x RS232 output, 0 x RS422 input, 0 x RS422 output,                                 |
| Opto-isolated lines         | 1 x Optical isolated input, 0 x Optical isolated input,                                               |
| I/O connector               | 12-pin Hirose HR10A-10P-12S                                                                           |
| Power supply                | 10 to 25VDC                                                                                           |
| Power consumption           | External: 17.5 W (typical)                                                                            |

## Operating conditions

|                                 |                 |
|---------------------------------|-----------------|
| Operating temperature (housing) | -10 °C to 60 °C |
|---------------------------------|-----------------|

## Mechanical properties

|                                   |               |
|-----------------------------------|---------------|
| Body dimensions (L x W x H in mm) | 130 × 69 × 69 |
| Filter/protection glass           | IR-Cut 680    |
| IP class                          | IP30          |
| Lens mount(s)                     | RF-Mount      |
| Weight                            | 350 g         |

## On-board memory and FPGA

|                             |            |
|-----------------------------|------------|
| Image buffer (RAM)          | 4032 MByte |
| Non-volatile memory (Flash) | 128 MByte  |

## Interfaces

|                     |                      |
|---------------------|----------------------|
| Digital interface   | 25gige               |
| Interface connector | (SFP28)              |
| Vision standard     | GigE Vision 2.0, 3.0 |

## FW features - image control

|                |                        |
|----------------|------------------------|
| Exposure modes | manual, auto, external |
|----------------|------------------------|

## FW features - image control

|            |              |
|------------|--------------|
| Gain modes | auto, manual |
|------------|--------------|

|                     |              |
|---------------------|--------------|
| White balance modes | auto, manual |
|---------------------|--------------|

|                        |                                              |
|------------------------|----------------------------------------------|
| Image control features | roi, lut, color-transformation, mirror-image |
|------------------------|----------------------------------------------|

## FW features - camera control

|                         |                                                  |
|-------------------------|--------------------------------------------------|
| Camera control features | PTP, RDMA support, User Sets, PWM(4), Sequencer, |
|-------------------------|--------------------------------------------------|

preliminary